

BC- 3G4UW302WKP30

4.4 卡

Description 产品描述:

- **3mm Round Lamp** 3mm 有边圆头灯
- **Lens Color** 胶体颜色: 白色散射
- **Emission Color** 发光颜色: **Ultra Bright Green** 甚高亮绿光
- **Viewing Angle** 半功率视角: **30°**
- **No Stopper** 无卡位
- **Dice Material** 晶片材质: **InGaN**

Absolute Maximum Ratings($T_a=25^{\circ}\text{C}$)最大限度性能参数($T_a=25^{\circ}\text{C}$)

Items 项	Symbol 符号	Absolute maximum Rating 最大限度	Unit 单位
DC Forward Current 正向电流*	I_F	20	mA
Peak Forward Current*正向峰值电流	I_{FP}	100	mA
Reverse Voltage 反向电压	V_R	5	V
Power Dissipation 消耗功率	P_D	72	mW
Operation Temperature 工作温度	T_{opr}	$-40\sim+85$	$^{\circ}\text{C}$
Storage Temperature 储存温度	T_{stg}	$-40\sim+100$	$^{\circ}\text{C}$
Lead Soldering Temperature	T_{sol}	Max. 260°C for 5 sec Max. (3mm from the base of the epoxy bulb) 最大 260°C 5 秒钟以内. (自胶体底部)	

*pulse width $\leq 0.1\text{msec}$ duty $\leq 1/10$ 脉冲宽度 $\leq 0.1\text{msec}$ 占空比 $\leq 1/10$

Typical Electrical & Optical Characteristics($T_a=25^{\circ}\text{C}$)产品光电特性($T_a=25^{\circ}\text{C}$)

Items 项目	Symbol 符号	Condition 条件	Min. 最小值	Typ. 平均值	Max. 最大值	Unit 单位
Forward Voltage 正向电压	V_F	$I_F = 20\text{mA}$	3.2	3.23	3.26	V
Reverse Current 反向电流	I_R	$V_R = 5\text{V}$	---	0.8		μA
Dominant Wavelength 主波长	λ_D	$I_F = 20\text{mA}$	---	520	---	nm
Luminous Intensity 发光强度	I_V	$I_F = 20\text{mA}$	---	2800	---	mcd
50% power Angle 半功率角度	201/2H-H	$I_F = 20\text{mA}$	---	30	---	deg
	201/2V-V	$I_F = 20\text{mA}$	---	---	---	deg

Rank Combination ($I_F=20mA$)档次分类($I_F=20mA$)

Luminous Rank 亮度分类	2000-3000			
	√			

*Measurement Uncertainty of Luminous Intensity: $\pm 10\%$
亮度误差 $\pm 10\%$

Unit 单位:mcd

Forward Voltage Rank 工作电压分类	3.2~3.26			
	√			

*Measurement Uncertainty of Forward Voltage: $\pm 0.1V$
电压误差 $\pm 0.1V$


Unit 单位:V

DominantWavelength RanK 主波长分类	515-520			
	√			

*Measurement Uncertainty of Dominant Wavelength $\pm 1.0nm$
主波长误差 $\pm 1.0nm$

Unit 单位:nm

Outline Drawing 外形图:



NOTES 备注:

1. All dimensions area in mm tolerance is $\pm 0.25\text{mm}$ unless otherwise no ted. 所有尺寸单位为 mm, 如无特殊说明误差范围为 $\pm .25$ mm.
2. An epoxy meniscus may extend about 0.5mm down the leads. 胶体沿支架延伸不可超过 0.5 mm.
3. Burr around bottom of epoxy may be 0.5mm max. 多胶不超过 0.5mm.